

HOW TO. ASSEMBLY GUIDE 2 DOOR METAL STORAGE CABINET

HT-6399

Each shelf can hold a maximum load of 45kg. Please carefully read and follow these instructions to assemble your cabinet.

ENSURE PROTECTIVE EYEWEAR AND GLOVES ARE WORN WHEN ASSEMBLING THIS UNIT.

WARNING: SERIOUS INJURY CAN BE CAUSED BY TOPPLING FURNITURE. To help prevent tip-over, we recommend you anchor this product to a wall or other suitable surface. Check anchors regularly.

Step 1

CHECK PARTS LIST

TOOLS REQUIRED:

- Rubber Mallet
- Phillips Head Screwdriver



1 x Front Panel (Doors & Frame)



1 x Rear Wall (install this way up & face detail towards inside of cabinet)



2 x Side Panel



(have folded edge)





2 x Plastic Covers 10 x Screws


16 x Shelf Supports 2 x Keys

Step 2

FITTING AND SECURING REAR WALL TO SIDES



Position the Right Side Panel next to the Rear Wall



View from above of how they slot together.



Secure with screws to hold side and rear together.



Repeat with other side

Step 3

FITTING FRONT PANEL TO SIDE **PANELS**












Slide Front Panel into the two sides and click into place

Step 4

FITTING AND SECURING TOP PANEL



Locate the Top Panel - the front has the 'push-through' slots. Lift the Top Panel into place from the inside



Fasten to the Back Panel with 3 x screws. Then, use a screwdriver to push the 'push-through' slots shown at 'A' into the Front Panel.

HOW TO. ASSEMBLY GUIDE 2 DOOR METAL STORAGE CABINET

HT-6399

Step 5

FITTING AND **SECURING THE FLOOR PANEL**



Place the Floor Panel into position with the cutouts facing the front.




Ensure the front lip goes over the top of the Front Panel





Turn the cabinet on its side and fasten the floor panel with one screw.

Step 6 FITTING THE **SHELVES**



Turn the cabinet upright and place the Shelf Supports into the side rails of the cabinet - 4 per shelf at the same height.



Place the Shelves onto the supports and ensure that they are locked into place.



Step 7 **FINISHING**

OFF



The doors have a spring loaded hinge to allow removal at any time. A cover is supplied for these access points. Simply push into place.

